



**HCC SERVICE DOUBLE ARM
COLUMN WITH TWO
SUBFUSES**

NOTES:

1. Individually fused to BS88-2, suitable size to the loading and protection of the cable.
2. Extension box may be required to assist with termination of the cables.
3. Test tags to be fitted indicating month and year of test and next test due date.
4. Telenso 1 part 5 wire communication node (Programmed to Hertfordshire) OSID number (TELENSA on drawing) to be affixed to the isolator, on the inside of the lantern and on the relevant paperwork.
5. Label locations shown are indicative only and subject to supply type characteristics.

Notes

A	Various drawing revisions	AS	RC	DOK	07/21
	Description	Dwn	Chk	App	Date

IWP No.					Drg. No. HST-1400-007					Rev. A	
	CAD	Drawn	Checked	Approved	Project Title						
Initials	PB	PB	ADS	PW	HCC STANDARD DETAIL DRAWINGS						
Date	01/10	04/10	04/10	04/10	Drawing Title						
Sht No.	1 OF 1				HCC CONNECTION WITH OUTGOING SOCKET						
Scales	NTS										



COUNTY HALL
Pegs Lane
Hertford, Herts
SG13 8DN
Phone: 01992 555555